

GENESISS ENGINEERS<sup>®</sup> Add - Office No.303,304,305 3<sup>Rd</sup> Floor, Vision9 mall, S.No.125/4,Kunal Icon Road, PimpleSaudagar, Pune.India.411027. E-mail - connect@genesissengineers.com Tel. - +91-20 - 27206635 / 36,9970600961

### Hydraulic Grip Front Loading Electronic Universal Testing Machine Model: UTE-HGFL

### **Features:**

- Open type cross head
- Hydraulic wedge action grips
- Long test stroke and dual test space
- Loading accuracy as high as + 1%
- Straining at variable speeds to suit a wide range of materials.
- Printer & PC graphs enable study the behavior of the material.
- Motor driven threaded columns for quick effortless adjustment of lower cross-head-to facilitate rapid fixing of test specimen.
- Simplicity in reading because of digital readouts.
- Wide range of standard and special accessories, including load stabilizer.
- Easy change from plain to threaded and screwed specimens.
- Large effective clearance between columns enables testing of standards specimens as well as structures.
- Simple controls for ease of operation.
- Robust straining frame of an extremely rigid construction.
- Safe operation ensured by means of safety devices.
- Fully enclosed and protected pressure transducer.
- RS 232 serial port to transfer data to computer for analysis/storage evaluation etc.
- Manual control & release valve operation.
- Load Capacity : 100 kN, 200 kN, 400 kN, 600 kN, 1000 kN and 1200 kN.

### **Application:**

Electronic Universal Testing Machine is designed for testing materials and other materials under tension, compression bending, transverse and shear loads. Hardness test on metals can also conducted.

### Machine Consists of -

### Straining unit:

This consists of a cylinder motor with chain and sprocket drive and a table coupled with the ram of the hydraulic cylinder, mounted on to a robust base.

The cylinder and the ram are individually lapped to eliminate friction. The upper cross-head is rigidly fixed to the table by two strengthened columns.

The lower cross-head is connected to two screwed columns which are driven by a motor. Axial loading of the ram is ensured by relieving the cylinder and ram of any possible side loading by the provision of ball seating. An displacement scale, with a minimum graduation of 1mm, is provided to measure the deformation of the specimen. Electronic Control Panel (Series Universal 2001-UTE) :



Microprocessor based panel incorporating state of art technology with following features -

- Front panel membrane type key board for machine operation with numeric keys for data entry.
  7 segment display.
- Data entry with numeric key board of test parameters including speeds, rupture % peak, pre-load, modulus data, test data & specimen data etc.
- 20 input data set storage, 50 result storage, maintains data & results during power off.

Tension test is conducted by gripping the test specimen between the upper and lower cross-heads.

Compression, transverse, bending, shear and hardness tests are conducted between the lower cross-head and the table.

The lower cross-head can be raised or lowered rapidly by operating the screwed columns, thus facilitating ease of fixing of the test specimen.

# Typical HGFL design includes a basic universal testing machine frame with open type crossheads and hydraulic wedge action grips.

### **Control Panel:**

The Control Panel consists of a power pack complete with drive motor and an oil tank, control valves and electronic display unit.

### **Power Pack:**

The power pack generates the maximum pressure of 200 kgf/cm2.

The hydraulic pump provides continuously non-pulsating oil flow. Hence the load application is very smooth.

### Hydraulic Controls:

Hand operated wheels are used to control the flow to and from the hydraulic cylinder.

The regulation of the oil flow is infinitely variable. Incorporated in the hydraulic system is a regulating valve, which maintains a practically constant rate of piston movement.

Control by this valve allows extensometer reading to be taken.

Another Power pack is used to operate wedge action grips by means of hydraulic cylinder by using solenoid valve operation

For Hydraulic Wedge action grips separate control remote is provided with selector switches indicating clamp – declamp and null positions.



GENESISS ENGINEERS<sup>®</sup> Add - Office No.303,304,305 3<sup>Rd</sup> Floor, Vision9 mall, S.No.125/4,Kunal Icon Road, PimpleSaudagar, Pune.India.411027. E-mail - connect@genesissengineers.com Tel. - +91-20 - 27206635 / 36, 9970600961

### Principle of Operation for -Model: UTE-HGFL

Operation of machine is by hydraulic transmission of load from the test specimen through pressure transducer to a separately housed load indicator.

The system is ideal since it replaces transmission of load through levers and knife edges, which are prone to wear and damage due to shock on rupture of test pieces.

Load is applied by a hydrostatically Lubricated ram. Main cylinder pressure is transmitted to the pressure transducer housed in the control panel.

The transducer gives the signal to the electronic display unit, corresponding to the load exerted by the main ram.

Simultaneously the encoder fitted on the straining unit gives the mechanical displacement to the electronic display unit.

Both the signals are processed by the microprocessor and load and displacement is displayed on the digital readouts simultaneously.

### Accuracy and Calibration:

Electronic Universal testing machine is closely controlled for sensitivity, accuracy and calibration during every stage of manufacture.

Machine is calibrated over each of its measuring range in accordance with the procedure laid down in British standards 1610: Part1: 1992 and IS 1828: Part1: 1991.

Electronic Universal Testing Machine complies with Grade "A" of BS: 1610:Part1:1992 and class 1 of IS-1828-Part1:1991.



Model: UTE-HGFL




GENESISS ENGINEERS<sup>®</sup> Add - Office No.303,304,305 3<sup>Rd</sup> Floor, Vision9 mall, S.No.125/4,Kunal Icon Road, PimpleSaudagar, Pune.India.411027. E-mail - connect@genesissengineers.com Tel. - +91-20 - 27206635 / 36, 9970600961

## Technical Specifications for -Hydraulic Grip Front Loading Electronic Universal Testing Machine Model: UTE-HGFL

Load resolution (2000 counts full scale)     N     5     10     20     30     50     60       Load range with accuracy of Measurement +/-1%     KN     2 to 100     4 to 200     8 to 400     12 to 600     20 to 1000     24 + 12 to 20 to 1000     20 to 1000     24 + 12 to 20 to 1000     20 to 1000     24 + 12 to 20 to 1000     20 to 1000     24 + 12 to 20 to 1000     20 to 1000     24 + 12 to 20 to 1000     20 to 1000     24 + 12 to 20 to 1000     20 to 1000     20 to 1000     20 to 1000     24 + 12 to 20 to 1000     20 t	MODEL	UNIT	UTE-HGFL 10	UTE-HGFL 20	UTE-HGFL 40	UTE-HGFL 60	UTE-HGFL 100	UTE-HGFL 1
Load resolution (2000 counts full scale)N5102030060Load range with accuracy of (besumement +/-1%)KN210 100410 200810 400121 600241 200Resolution of pison movement (Displacement) of UTEmm0.10.	Maximum Capacity	kN	100	200	400	600	1000	1200
(20000 counts full scale)N5N020309000Laad range with accuracy of Measurement (1%) (Despinement) for UTEkN210 100810.400121 06002010.100024.1200Resolution of piston movement (Displacement) for UTEmm0.10.10.10.10.10.10.10.10.10.1Clearance for emple sett (Attuly descended working piston)mm50-70050-70050-70050-800 <td< td=""><td>Measuring range</td><td>kN</td><td>0-100</td><td>0-200</td><td>0-400</td><td>0-600</td><td>0-1000</td><td>0-1200</td></td<>	Measuring range	kN	0-100	0-200	0-400	0-600	0-1000	0-1200
Measurement 4/-1%MMZ 0 1004 10 2006 10 40012 10 00020 10 100024 10 000Resolution of piston movement (Obspiacement) for UTEmm0.10.10.10.10.10.10.1Clearance for compression test (Attily descended working piston)mm50-70050-70050-80050-800-0-85050-850Clearance for compression test (Attily descended working piston)mm5005005006000750750Clearance between columnsmm5005000-1500-1000-8000-850250Clearance between columnsmm/min0-3000-1500-1000-8000-8500-850CONNECTED LOADmm/min0-3002.333.333.53.53.5V0400-440400-440400-440400-440400-440400-4400400-400400-440400-440400-440400-440400-4400400-400400-440400-440400-440400-440400-4400400-400400-440400-440400-440400-440400-4400400-400400-400400-400400-440400-440400-4400400-400400-400400-400400-400400-400400-4400400-400400-400400-400400-400400-400400-4000400-400400-400400-400400-400400-400400-400040		Ν	5	10	20	30	50	60
(Displacement) for UTEInitialO.1		kN	2 to 100	4 to 200	8 to 400	12 to 600	20 to 1000	24-1200
(At fully descended working piston)mm50-70050-70050-70050-80050-85050-850Clearance for compression test (At fully descended working piston)mm0-7000-7000-8000-08000-8500-850Clearance between columnsmm500000000600750750Ram Strokemm0-3000-1500-1000-8000-6800-685CONNECTED LOADmm/min0-3000-1500-1000-8000-685CONNECTED LOADHP2.332.333.53.53.53.5VMover400-400400-440400-440400-440400-440\$PowerHP2.332.333.33.53.53.5VMover10-2010-2010-2010-2010-2010-20\$Gamping javes for round specimens of diameter10-2010-2010-2010-2010-2010-2010-20Clamping javes for flat specimens of thickness10-2010-2010-2010-2010-2010-2010-2010-20Clamping javes for flat specimens of thickness10-2010-2010-2010-2010-2010-2010-20Clamping javes for flat specimens of thickness10-2010-2010-2010-2010-2010-2010-20Clamping javes for flat specimens of thickness10-2010-2010-2010-2010-2010-2010-20Clamping javes for flat sp		mm	0.1	0.1	0.1	0.1	0.1	0.1
(Atfully descended working piston)Mm0-7000-7000-8000-8000-8500-850Clearance between columnsmm500500500600750750Ram Strokemm150200200250250250Straining/ Piston Speed (at no load)mm/min0-3000-1500-1000-8000-650CONNECTED LOADmm/min0-3002.333.333.53.53.5VMP2.332.333.333.53.53.5VMP2.333.333333STANDARD ACCESSORIES10-2010-2010-2010-2010-2010-20Clamping jaws for round specimens110-2010-2010-2010-2020-3020-30Clamping jaws for flat specimens110-2010-2010-2010-2010-2010-20Clamping jaws for flat specimens110-2010-2010-2010-2010-2010-20Clamping jaws for flat specimens110-2010-2010-2010-2010-2010-20Midthmm1010-2010-2010-2010-2010-2010-20Clamping jaws for flat specimensmm10-2010-2010-2010-2010-20Grading jaws for flat specimensmm10-2010-2010-2010-2010-20Clamping jaws for flat specimensmm10-2010-2010-20		mm	50-700	50-700	50-700	50-800	50-850	50-850
Ram Strokemm150200250250250Straining/ Piston Speed (at no load)mm/min0-3000-1500-1500-1000-800-65CONNECTED LOAD3.333.53.53.53.5PowerHP2.332.333.333.53.53.53.5V400-400400-400400-400400-400400-400400-400400-400400-400Φ400400-400400-400400-400400-400400-400400-400400-400Φ4003.33 <td>Clearance for compression test (At fully descended working piston)</td> <td>mm</td> <td>0-700</td> <td>0-700</td> <td>0-700</td> <td>0-800</td> <td>0-850</td> <td>0-850</td>	Clearance for compression test (At fully descended working piston)	mm	0-700	0-700	0-700	0-800	0-850	0-850
Straining/ Piston Speed (at no load)mm/min0-3000-1500-1000-8000-68CONNECTED LOADPowerP2.333.333.53.53.53.5V0400-400400-400400-400400-400400-400400-400400-400400-400000003333333STANDARD ACCESSORIES5555555555555555555555555555666<	Clearance between columns	mm	500	500	500	600	750	750
Straining/ Piston Speed (at no load)mm/min0-3000-1500-1600-8000-86CONNECTED LOADPowerPMP2.333.333.53.53.53.5V0400-400400-400400-400400-400400-400400-400400-400400-400Φ0333333333STANDARD ACCESSORIES555555555FOR TENSION TEST55555666666Clamping jaws for round specimens of diameterMm10-2010-2010-2010-2020-30 <td>Ram Stroke</td> <td>mm</td> <td>150</td> <td>200</td> <td>200</td> <td>250</td> <td>250</td> <td>250</td>	Ram Stroke	mm	150	200	200	250	250	250
PowerHP2.332.333.333.53.5V400-400400-400400-400400-400400-400400-400400-400Φ33333333STANDARD ACCESSORIES5555555FOR TENSION TEST5555555Of diameter710-2010-2010-2010-2020-3020-3020-30Of diameter7610-2020-3020-3020-3020-3020-3020-30Of diameter7610-2020-3020-3020-3020-3020-3020-3020-30Of diameter7610-2010-2010-2010-2020-3020-3020-3020-3020-30Of diameter777777777777Of diameter710-2010-2010-2010-2010-2010-2020-30<	Straining/ Piston Speed (at no load)	mm/min	0-300					0-65
VV400-440400-440400-440400-440400-440400-440400-440 $\Phi$ 333333333STANDARD ACCESSORIESFOR TENSION TEST <td>CONNECTED LOAD</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td>	CONNECTED LOAD							
Φ3333STANDARD ACCESSORIESFOR TENSION TESTClamping jaws for round specimens of diameter10-2010-2010-2010-2010-2020-3020-3020-3020-3020-3020-3020-3020-30Clamping jaws for round specimens of diameter30-4030-4030-4030-4030-4030-4030-4030-4030-4040-5040-5040-5040-5040-5010-2010-2010-2010-2010-2010-2010-2010-2010-20	Power	HP	2.33	2.33	3.33	3.5	3.5	3.5
STANDARD ACCESSORIES     FOR TENSION TEST     10-20     20-30	V		400-440	400-440	400-440	400-440	400-440	400-440
FOR TENSION TESTImage: state	Φ		3	3	3	3	3	3
$ \begin{tabular}{ c c c c } \hline \begin{tabular}{ c c c c } \hline \begin{tabular}{ c c c c } lic) lic) lic) lic) lic) lic) lic) lic)$	STANDARD ACCESSORIES							
$ \begin{array}{c c c c c c c } \mm & 20-30 & 20-30 & 20-30 & 20-30 & 20-30 & 20-30 & 20-30 & 20-30 & 20-30 & 20-30 & 20-30 & 00-40 & 00-$	FOR TENSION TEST							
of diameter     Imm     Imm <t< td=""><td rowspan="8">of diameter Clamping jaws for flat specimens</td><td></td><td>10-20</td><td>10-20</td><td>10-20</td><td>10-20</td><td>10-20</td><td>10-20</td></t<>	of diameter Clamping jaws for flat specimens		10-20	10-20	10-20	10-20	10-20	10-20
Image: constraint of the specimens of thickness     Image: constraint of the specimens of the specimens of thickness     Image: constraint of the specimens of the specimens of the specimens of thickness     Image: constraint of the specimens of th		mm	20-30	20-30	20-30	20-30	20-30	20-30
$ \begin{array}{c c c c c c c c c c c c c c c c c c c $					30-40	30-40	30-40	30-40
$ \begin{array}{c c c c c c c c c c c c c c c c c c c $							40-50	40-50
of thickness     mm     mm     mm     mm     mm     mm     20-30     20-30     20-30     20-30     20-30     20-30     20-30     20-30     30-40			0-10	0-10	0-10	0-10	0-10	0-10
Minimum clearance between supports     mm     500     20-30     30-40 <t< td=""><td>mm</td><td>10-20</td><td>10-20</td><td>10-20</td><td>10-20</td><td>10-20</td><td>10-20</td></t<>		mm	10-20	10-20	10-20	10-20	10-20	10-20
Width     mm     50     50     65     70     70     70       FOR COMPRESSION TEST     mm     120     120     120     120     160     160       Pair of Compression Plates of diameter.     mm     120     120     120     160     160       FOR TRANSVERSE TEST     mm     120     160     160     160     160       Table with adjustable rollers     mm     160					20-30	20-30	20-30	20-30
FOR COMPRESSION TESTImage: Second							30-40	30-40
Pair of Compression Plates of diameter.     mm     120     120     120     120     160     160       FOR TRANSVERSE TEST     Image: Compression Plates of diameter.     Image: Compression Plates of	Width	mm	50	50	65	70	70	70
FOR TRANSVERSE TEST Table with adjustable rollersImage: Second S								
Table with adjustable rollers     width of rollers   mm   160	Pair of Compression Plates of diameter.	mm	120	120	120	120	160	160
width of rollers     mm     160								
Diameter of Rollersmm3030305050Maximum clearance between supportsmm500500500600800800	Table with adjustable rollers							
Maximum clearance between supports     mm     500     500     600     800     800	width of rollers	mm	160	160	160	160	160	160
	Diameter of Rollers	mm	30	30	30	50	50	50
Radius of punch tops     mm     6,12     6,12     12,16     16,22     16,22     16,22	Maximum clearance between supports	mm	500	500	500	600	800	800
	Radius of punch tops	mm	6,12	6,12	12,16	16,22	16,22	16, 22




### Optional Software Package - Tension & Compression test Software package for Model: UTE-HGFL




### **Control Parameters**

### **Real Time Graph**



Real time values of load & displacement/extension used for plotting its graph & can be seen real time during testing.

### Graph Superimpose with Point Tracing



Graph comparison, superimpose of batch sample tests with point tracing facility.

# A reach Link link link Annu Ann

Displays graph for extensometer readings against load with proof lines for proof stress.

Statistics



Batch test reports with statistics for batch sample results.

Windows based software available for -Online graph on PC, Data analysis, Statistics, Point tracing, superimposing graphs to compare with standard, zooming graph etc.

### Load Vs Extension